

# tesa® 6300

## product information



### Hand dispenser for packaging tapes

The tesa® 6300 hand dispenser is a good value dispenser for professional sealing with all kinds of tesa® packaging tapes in packaging and production areas. The dispenser has a tension control so that even easy unwinding tesa® tapes can be used without difficulty. The blade is covered to prevent injury.

### Main Application

Place the dispenser on the carton and pull it towards yourself. The rubber contact roller presses the tape down firmly as it is applied from the roll. The tape is cut by the serrated blade by tilting the dispenser. The cut end of the tape is pressed to the carton by the flexible application plate. Threading: the tesa® roll is put on the tape wheel such that the adhesive side of the tape faces the handle. Pull the end of the tape between the tape guide roller and the metal plate until the tape is free of wrinkles.

### Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

#### Technical Data

• Core diameter	3 inch	• Mode of drive	manual
• Type of tape	single-sided	• Weight	350 g
• Application purpose	packaging	• Max. roll diameter	120 mm
• Length	150 mm	• Type of applicator	hand
•	65 mm	• Max. roll width	50 mm
•	240 mm		

### Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit  
<http://l.tesa.com/?ip=06300>